

## C-Mount Camera – HDMI KERN ODC-85



### Features

- The ODC 851 HDMI microscope camera has been specially developed for direct HDMI connection to your HDMI compatible display device. The images can be stored straight onto the SD card which is delivered with the product or can be transferred to your PC or laptop for further processing using the USB 2.0 cable in combination with the OXM 902 software
- The HDMI autofocus camera ODC 852 offers you a perfect, effective solution for modern microscopy. The autofocus function automatically detects and adjusts the focus level so that you always have a razor-sharp image. Ideal for all applications in connection with a KERN stereo microscope
- Realtime images can be transferred to an HD-MI-compatible display device using the HDMI connection and they can also be stored on the SD card which was delivered with the product.

- As an alternative, data can also be transferred using the WiFi module (ODC 852) to a PC or laptop in combination with the KERN OXM 902 software which is included with the delivery
- Power supply is from an external 12 V power unit
- Scope of delivery ODC 851: Camera, USB mouse, USB 2.0 cable (length: 2 m), HDMI cable (length: 2 m), SD card (16 GB)
- Scope of delivery ODC 852: Camera, USB mouse, HDMI cable (length: 2 m), SD card (16 GB), WiFi adapter and camera software Microscope VIS Pro KERN OXM 902
- Please order the appropriate C-mount adapter to fit your KERN microscope now

STANDARD



Model	Resolution	Interface	FPS	Sensor	Sensor size	Colour/ Monochrome	Supported operating system
<b>KERN</b>							
ODC 851*	2 MP	HDMI, USB 2.0, SD	60	CMOS	1/2"	colour	Win XP, Vista, 7, 8, 10
ODC 852	5 MP	HDMI, SD, WLAN	25 – 60	CMOS	1/1,8"	colour	Win XP, Vista, 7, 8, 10

! \* ONLY WHILE STOCKS LAST

## C-Mount Camera – High Resolution KERN ODC-86



## The cooled camera for professional fluorescence examinations

### Features

- The ODC 861 camera with Peltier cooling technology has been specially designed for fluorescent applications. It is able to significantly compensate for image noise associated with weak lighting. Due to its high resolution and light-sensitive Sony CMOS colour sensor it proves first-class images. The practical, sturdy storage box serves as protection and for transportation of this premium camera

- Realtime images can be transferred straight to a PC or laptop using the integrated USB 3.0 interface. As an alternative, 2 USB 2.0 interfaces are available, to operate the camera with the OXM 902 software
- Power supply is from an external 12 V power unit
- Please order the appropriate C-mount adapter (only 1,0x possible) to fit your KERN microscope now
- Black balance possible

**Note:** Can only be used in combination with compound microscopes

STANDARD



Model	Resolution	Interface	FPS	Sensor	Sensor size	Colour/ Monochrome	Supported operating system
<b>KERN</b>							
ODC 861	20 MP	USB 3.0	5 – 30	CMOS	1"	colour	Win XP, Vista, 7, 8, 10

